### Rittal – The System.

Faster – better – everywhere.





## TS 8165.235 Side wall, screwable, carbon steel

State: 2025-11-04 (Source: rittal.com/ca-en)



# TS 8165.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

#### **Features**

Model No.	TS 8165.235	
Benefits	Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert Easy positioning with the location aid Grounding bolt with contact surface	
Material	Carbon steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Color	RAL 7035	
Supply includes	Assembly components	
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure.  Area available for population: External dimension – 100 mm	
Suitable for	Enclosure type: TS TS IT Height: 1,600 mm Depth: 500 mm	
Protection category IP to IEC 60 529	IP 55	
Base material	Carbon steel	
Packaging unit	2 pc(s).	
Net weight	18.6	
Gross weight	19.8	
Customs tariff number	94039910	
EAN	4028177386723	

© Rittal 2025

### **Features**

ETIM 9	EC002524	
ECLASS 8.0	27182101	

© Rittal 2025 3