

Rittal – The System.

Faster – better – everywhere.



TS 8601.050

Base/plinth trim panels, side, 100 mm

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8601.050 - Base/plinth trim panels, side, 100 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used. Base/Plinth panels can be installed turned at 90° to provide stabilization for bayed base/plinth components.

Features

| | |
|-----------------------|---|
| Model No. | TS 8601.050 |
| Product description | To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 7022 |
| Supply includes | 2 plinth/base trim panels Assembly components |
| Mounting tip | 100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here |
| Dimensions | Height: 100 mm |
| Suitable for | Enclosure type: TS: = 500 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT |
| Packaging unit | 2 pc(s). |
| Net weight | 1.436 kg |
| Gross weight | 1.636 kg |
| Customs tariff number | 94039910 |

Features

ECLASS 8.0

27182003

Product description

TS Trim panel, sides, H: 100 mm, for W: 500 mm, RAL 7022, sheet steel