
### Rittal – The System.

Faster – better – everywhere.





### TS 8602.080

# Base/plinth trim panels, side, 200 mm

State: 2025-11-24 (Source: rittal.com/ca-en)



## TS 8602.080 - Base/plinth trim panels, side, 200 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used.

#### **Features**

To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used.  Carbon steel  Spray-finished
Spray-finished
RAL 7022
2 plinth/base trim panels Assembly components
100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here
Height: 200 mm
Enclosure type: TS: = 800 mm  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: TS IT
2 pc(s).
4.454
4.654
94039910
4028177208704

© Rittal 2025

### Features

ECLASS 8.0

27182003

© Rittal 2025 3