

Rittal – The System.

Faster – better – everywhere.



TS 8602.400

Base/plinth components, front and rear, 200 mm

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8602.400 - Base/plinth components, front and rear, 200 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.

Features

Model No.	TS 8602.400
Version	Solid
Product description	Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.
Material	Base/plinth components: Carbon steel Cover caps: Plastic
Surface finish	Spray-finished
Color	RAL 7022 Cover caps: RAL 9005
Supply includes	2 base/plinth components 4 cover caps Assembly components
Dimensions	Height: 200 mm
Suitable for	Enclosure type: TS: = 400 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT
Packaging unit	2 pc(s).
Net weight	4.54 kg
Gross weight	5.622 kg
Customs tariff number	94039910

Features

ECLASS 8.0

27182003

Product description

TS Base/plinth component, front and rear, H: 200 mm, for W: 400 mm, RAL 7022, sheet steel