### Rittal – The System.

Faster – better – everywhere.





### TS 8602.600

# Base/plinth components, front and rear, 200 mm

State: 2025-10-26 (Source: rittal.com/ca-en)



## TS 8602.600 - Base/plinth components, front and rear, 200 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.

#### **Features**

Model No.	TS 8602.600
Version	Solid
Product description	Base/Plinth component consisting of one trim panel and two pre- assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.
Material	Base/plinth components: Carbon steel Cover caps: Plastic
Surface finish	Spray-finished
Color	RAL 7022 Cover caps: RAL 9005
Supply includes	2 base/plinth components 4 cover caps Assembly components
Dimensions	Height: 200 mm
Suitable for	Enclosure type: TS: = 600 mm  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: TS IT
Packaging unit	2 pc(s).
Net weight	6.32
Gross weight	6.963
Customs tariff number	94039910

© Rittal 2025 2

### **Features**

EAN	4028177208612
ECLASS 8.0	27182003

© Rittal 2025 3