

Rittal – The System.

Faster – better – everywhere.



TS 8610.825 Glazed Door

State: 2025-07-28 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.825 - Glazed Door for TS, TS IT, VX SE

Alternative to a carbon steel door or rear wall.



Features

Model No.	TS 8610.825
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminum section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door frame with safety glass Locking rod with double-bit insert 180° hinges (4 pcs)
Visible area	Viewing window width: 660 mm Viewing window height: 2,040 mm
Viewing window height	2,040 mm

Features

Mounting tip	When mounting instead of the rear panel, the lock components are required
Protection category IP to IEC 60529	IP 55
Suitable for	Enclosure type: TS TS IT VX SE Width: = 800 mm Height: = 2,200 mm
Packaging unit	1 pc(s).
Net weight	19
Gross weight	20
EAN	4028177693876
ETIM 9	EC000747
ECLASS 8.0	27182204