


Rittal – The System.

Faster – better – everywhere.



TS 8612.660

TS Mounting Chassis, 45 x 88 mm

State: 2026-05-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.660 - TS Mounting Chassis, 45 x 88 mm

Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

Model No.	TS 8612.660
Version	For the inner mounting level
Product description	Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The double profile with 11 rows of holes provides many additional options for interior configuration.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	On the vertical and horizontal TS, VX SE enclosure section
Suitable for	Enclosure type: the inner mounting level Width/depth: 600 mm
Packaging unit	2 pc(s).
Net weight	2.8 kg
Gross weight	3.02 kg
Customs tariff number	73269098
ETIM 9	EC002625

Features

ECLASS 8.0

27189234

Product description

TS TS punched section without mounting flange, 45 x 88 mm, for inner mounting level: for WD: 600 mm