

Rittal – The System.

Faster – better – everywhere.



VX 8619.780

System chassis 14 x 39 mm

State: 2026-05-28 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.780 - System chassis 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

Model No.	VX 8619.780
Product description	For securing cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between fixing points	1,275 mm
Installation options AX	In enclosure height 1400 mm, in conjunction with rail for interior installation AX
Installation options AX stainless steel	In enclosure height 760 mm
Mounting tip	For installation in AX carbon steel, only in conjunction with rails interior installation AX
Note	Carbon steel screws or M5 self-tapping screws are required for extension with own components on the system chassis
Suitable for	Enclosure type: AX Suitable for width or height or depth: 1,400 mm

Features

Packaging unit	4 pc(s).
Net weight	2.44 kg
Gross weight	2.7 kg
PCF/VE (cradle-to-gate)	19.76
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section with mounting flange, 14 x 39 mm , for H: 1400 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------