

Rittal – The System.

Faster – better – everywhere.



TS 8628.548

Baying systems TS 8

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8628.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

Features

Model No.	TS 8628.548
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: powder-coated Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Base Plates Mounting plate
Dimensions	Width: 600 mm Height: 2,200 mm Depth: 800 mm
Protection category NEMA	NEMA 3R
Packaging unit	1 pc(s).
Customs tariff number	9403200082

Approvals

Approvals

UL + C-UL (listed)