
### Rittal - The System.

Faster – better – everywhere.





# VX 8640.031 Page/plinth trim panels, side

# Base/plinth trim panels, side, 100 mm

State: 2025-12-03 (Source: rittal.com/ca-en)



## VX 8640.031 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

#### **Features**

Model No.	VX 8640.031
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm
Suitable for	Depth: = 400 mm
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	0.98 kg
Packaging unit	2 pc(s).
Net weight	0.9
Gross weight	0.96
Customs tariff number	94039910
EAN	4028177958937
E-Number Sweden	E3465377
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2

## Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 3