Rittal – The System.

Faster – better – everywhere.





VX 8640.040 Base/plinth trim panels, side, 200 mm

State: 2025-11-13 (Source: rittal.com/ca-en)



VX 8640.040 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.

Features

Model No.	VX 8640.040
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 200 mm
Suitable for	Depth: = 300 mm
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	1.12 kg
Packaging unit	2 pc(s).
Net weight	1.1
Gross weight	1.124
Customs tariff number	94039910
EAN	4028177959019
E-Number Sweden	E3465383
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2

Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 3