

Rittal – The System.

Faster – better – everywhere.



TS 8800.570 Cable duct

State: 2026-05-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8800.570 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.



Features

Model No.	TS 8800.570
Version	Width 50 mm, for assembly on a vertical enclosure section in the side panel area.
Benefits	<p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p>
Material	Hard PVC Flame-resistant, self-extinguishing
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm
Slot width	4.5 mm
Note	Can be shortened for other enclosure sizes.

Features

Dimensions	Width: 50 mm Height: 1,600 mm Depth: 80 mm
Suitable for	Enclosure type: TS VX SE PC IW Height: ≤ 1,800 mm
Operating temperature range	60 °C
Packaging unit	8 pc(s).
Net weight	8.968 kg
Gross weight	9.44 kg
Customs tariff number	39259020
ETIM 9	EC000012
ECLASS 8.0	27400703
Product description	TS Cable duct for vertical TS section, WHD: 50x1600x80 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---