

# Rittal – The System.

Faster – better – everywhere.



## TS 8800.680 EMC Base Plate

State: 2025-08-26 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.680 - EMC Base Plate

For shielded cables with max. 20 mm diameter in combination with standard base plates.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | TS 8800.680   |
| Product description   | For shielded cables with max. 20 mm diameter. Combined EMC contacting and cable fixation provide low-impedance contact between the cable shield and the base plate. For all 400, 500, 600 and 800 mm deep enclosures, in combination with standard base plates. |
| Material              | Carbon steel  |
| Surface finish        | Zinc-plated   |
| Supply includes       | Cable management rail with T-head punching<br>1 sliding base plate<br>2 EMC seals   |
| Suitable for          | Enclosure type: TS<br>Width: = 800 mm   |
| Note                  | No standard-compliant IP protection rating possible   |
| Packaging unit        | 1 pc(s).  |
| Net weight            | 2.4   |
| Gross weight          | 2.554   |
| Customs tariff number | 94039910  |
| EAN                   | 4028177214897   |
| ETIM 9                | EC002620  |
| ECLASS 8.0            | 27189261  |