
## Rittal - The System.

Faster - better - everywhere.





## PC 8800.920 Base/plinth, stationary

State: 2025-11-29 (Source: rittal.com/ca-en)



## PC 8800.920 - Base/plinth, stationary for PC, IW

Design matches the housing, height 100 mm, with front projection.

## **Features**

Model No.	PC 8800.920
Product description	Design matches the housing, with front projection.
Material	Carbon steel, 2.0 mm
Color	RAL 7035 Design component, front: RAL 7015
Supply includes	1 design component, front 1 base/plinth component, rear 2 base/plinth trim panels, side
Dimensions	Height: 100 mm
Suitable for	Enclosure type: PC IW Width: = 600 mm Depth: = 600 mm
Suitable for depth	600 mm
Packaging unit	1 pc(s).
Net weight	11.92
Gross weight	13.02
PCF/VE (cradle-to-gate)	49.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177266926
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025