

Rittal – The System.

Faster – better – everywhere.



PC 8800.920

Base/plinth, stationary

State: 2026-01-16 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

PC 8800.920 - Base/plinth, stationary for PC, IW

Design matches the housing, height 100 mm, with front projection.

Features

Model No.	PC 8800.920
Product description	Design matches the housing, with front projection.
Material	Carbon steel, 2.0 mm
Color	RAL 7035 Design component, front: RAL 7015
Supply includes	1 design component, front 1 base/plinth component, rear 2 base/plinth trim panels, side
Dimensions	Height: 100 mm
Suitable for	Enclosure type: PC IW Width: = 600 mm Depth: = 600 mm
Suitable for depth	600 mm
Packaging unit	1 pc(s).
Net weight	11.92
Gross weight	13.02
PCF/VE (cradle-to-gate)	49.5 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177266926
ETIM 9	EC000721
ECLASS 8.0	27182003