

Rittal – The System.

Faster – better – everywhere.



TS 8801.180

Partial Doors

State: 2026-03-14 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP



TS 8801.180 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

Model No.	TS 8801.180
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm
Color	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly components
Dimensions	Width: 800 mm Height: 800 mm

Features

Protection category IP to IEC 60529	IP 54 for a completed enclosure
-------------------------------------	---------------------------------

Packaging unit	1 pc(s).
----------------	----------

Net weight	6.888 kg
------------	----------

Gross weight	7.25 kg
--------------	---------

Customs tariff number	94039910
-----------------------	----------

ETIM 9	EC000747
--------	----------

ECLASS 8.0	27182204
------------	----------
