Rittal – The System.

Faster - better - everywhere.





DK 9055.312 Monitor/Keyboard Unit

State: 2025-11-19 (Source: rittal.com/ca-en)



DK 9055.312 - Monitor/Keyboard Unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



Features

Model No.	DK 9055.312
Product description	Maximum power consumption during operation without optional KVM switch: 32 W, maximum power consumption when closed, without optional KVM switch: < 1 W.
Benefits	Analog and digital video port
	Cables are safely routed in the energy chain
	Lockable at the front
	Simple, one-man installation.
Color	RAL 7035
Supply includes	Monitor/Keyboard Unit, 1 U
	VGA cable
	DVI cable
	USB Cable
	Schuko power cable
	with 17" TFT display and VGA/DVI connection
	2 PS/2 cables
	Keyboard
	with integral touchpad
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Max. power consumption with closed monitor unit	1 W

© Rittal 2025

2

Features

Max. power consumption in operation	32 W
Interfaces	VGA (D-SUB HD 15-pole)
	DVI
	1 x USB
	PS/2
Connector (type)	Non-heating apparatus connector C14
Layout	US English
Dimensions	Width: 482.6 mm
	Depth: 680 mm
Operating temperature range	5 °C45 °C
Installation dimensions	Installation depth (min.): 680 mm
	Installation depth (max.): 850 mm
Display features	Diagonal: 432 mm (17")
	Format: 4:3
	Contrast ratio: Contrast ratio approx. 1000:1
	Display brightness: 350 cd/m²
	Display resolution: 1280 x 1024 pixels
	Number of colors: 16,700,000
Packaging unit	1 pc(s).
Net weight	15.85
Gross weight	17.25
Customs tariff number	85286200
EAN	4028177638389
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

Explanations	Declaration of conformity
--------------	---------------------------

© Rittal 2025 3