


# Rittal – The System.

Faster – better – everywhere.



## KEL 9202.600 Ex Enclosures

State: 2024-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9202.600 - Ex Enclosures Plastic, empty enclosure with hinged door

Ex Housing with Hinged Door, Plastic



## Features

Model No.	KEL 9202.600
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)
Material	Housing: fiber-glass reinforced unsaturated polyester, surface resistance: < 10 <sup>11</sup> Ω Door: fiber-glass-reinforced unsaturated polyester, surface resistance: < 10 <sup>11</sup> Ω, all-round foamed-in silicone seal Mounting plate: Carbon steel, zinc-plated
Color	RAL 9011
Supply includes	Housing Door Mounting plate
Dimensions	Width: 250 mm Height: 350 mm Depth: 150 mm
Dimensions of mounting plate (W x H)	195 mm x 300 mm

# Features

Certificate IEC EX PTB 10.0011U	Yes
Certificate PTB 03 ATEX 1011U	Yes
Base material	Plastic
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Protection category IP to IEC 60 529	IP 66
Packaging unit	1 pc(s).
Weight/packaging unit	4.6 kg
Customs tariff number	94037000
EAN	4028177138247
ETIM 7.0	EC002503
ECLASS 8.0	27180502

# Approvals

Approvals	ATEX
Certificates	Protection category
Explanations	Manufacturer's declaration