Rittal – The System.

Faster – better – everywhere.





SV 9340.010 Busbar Supports

State: 2025-10-16 (Source: rittal.com/ca-en)



SV 9340.010 - Busbar Supports For Flat Copper Busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.010
Material	Polyamide
	Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Note on Model No.:	When $12 \times 5/10 $ mm busbars are used, spacer 9340.090 must also be used
Number of poles	3-pole
With external attachment	Yes
Center-to-center spacing of busbars	60 mm
Suitable for busbars	15 x 5 - 30 x 10
Packaging unit	4 pc(s).
Net weight	0.76
Gross weight	0.8
Customs tariff number	85369010
EAN	4028177502338
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

© Rittal 2025

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3