

Rittal – The System.

Faster – better – everywhere.



SV 9340.030 Busbar Supports

State: 2025-08-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.030 - Busbar Supports 1-pole

Features

Model No.	SV 9340.030
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Suitable for busbars	12 x 5/10 15 x 5 - 30 x 10
Suitable for busbars	Flat copper busbars
Number of poles	1-pole
Note	Multi-pole systems with 60 mm busbar center-to-center distances can be created by buying the busbar supports Support suitable for AC and DC applications.
Note on Model No.:	When 12 x 5/10 mm busbars are used, spacer 9340.090 must also be used
Rated operating voltage	1000 V, 1~ 1500 V (DC)
PEN/N/PE support	Yes
Packaging unit	4 pc(s).
Net weight	0.2
Gross weight	0.24
Customs tariff number	85369010
EAN	4028177583580
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals

ABS
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK