Rittal – The System.

Faster – better – everywhere.





SV 9340.030 Busbar Supports

State: 2025-10-30 (Source: rittal.com/ca-en)



SV 9340.030 - Busbar Supports 1-pole

Features

| Model No. | SV 9340.030 |
|-------------------------|---|
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Suitable for busbars | 12 x 5/10 15 x 5 - 30 x 10 |
| Suitable for busbars | Flat copper busbars |
| Number of poles | 1-pole |
| Note | Multi-pole systems with 60 mm busbar center-to-center distances can be created by baying the busbar supports Support suitable for AC and DC applications. |
| Note on Model No.: | When 12 x 5/10 mm busbars are used, spacer 9340.090 must also be used |
| Rated operating voltage | 1000 V, 1~ 1500 V (DC) |
| PEN/N/PE support | Yes |
| Packaging unit | 4 pc(s). |
| Net weight | 0.2 |
| Gross weight | 0.24 |
| Customs tariff number | 85369010 |
| EAN | 4028177583580 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |
| | |

© Rittal 2025

Approvals

| Approvals | ABS |
|--------------|------------------------------|
| | DNV-GL |
| | Lloyds Register of Shipping |
| | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

© Rittal 2025 3