## Rittal – The System.

Faster - better - everywhere.





# SV 9340.510 OM adapter

State: 2025-11-18 (Source: rittal.com/ca-en)



## SV 9340.510 - OM adapter with tension spring clamp



#### **Features**

Model No.	SV 9340.510
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to- center spacing	60 mm
Support rail type	Without support frame, 1 x TS 45C
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm²
Support rails Qty/height	1 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Packaging unit	1 pc(s).
Net weight	0.231
Gross weight	0.24
Copper weight (kg per piece)	0.027

© Rittal 2025

### Features

Customs tariff number	85369095
EAN	4028177502611
ETIM 9	EC001531
ECLASS 8.0	27370304

## **Approvals**

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3