

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.520 OM adapter

State: 2026-05-11 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.520 - OM adapter with tension spring clamp



## Features

Model No.	SV 9340.520
Version	with tension spring clamp
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Without support frame, 2 x TS 45D
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Packaging unit	1 pc(s).
Net weight	0.238 kg
Gross weight	0.266 kg

# Features

---

Copper weight (kg per piece)	0.027
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm <sup>2</sup> , WH: 45x208 mm, support rail 2xTS 45D

# Approvals

---

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK