


Rittal – The System.


Faster – better – everywhere.



SV 9340.530

OM adapter

State: 2026-02-03 (Source: rittal.com/ca-en)



SV 9340.530 - OM adapter with tension spring clamp



Features

Model No.	SV 9340.530
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, 1 x TS 45C
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm ²
Support rails Qty/height	1 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Packaging unit	1 pc(s).
Net weight	0.259
Gross weight	0.28

Features

Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177502628
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK