

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.560 OM adapter

State: 2025-12-17 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.560 - OM adapter with tension spring clamp



## Features

Model No.	SV 9340.560
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 45 mm Height: 272 mm
Connection of round conductors	1.5 - 6 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 237 mm
Packaging unit	1 pc(s).
Net weight	0.28

# Features

Gross weight	0.293
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177664234
ETIM 9	EC001531
ECLASS 8.0	27370304

# Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK