

# Rittal – The System.

Faster – better – everywhere.



## SV 9342.004 PLS Busbar Supports

State: 2025-07-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.004 - PLS Busbar Supports

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.

## Features

Model No.	SV 9342.004
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Electrical UL ratings (SCCR)	65 kA - 480 V, support spacing 250 mm, busbars PLS 1600, circuit breaker max. 1200A, DIVQ/7
Note on Model No.:	The use of a base tray is required for UL applications. UL approval only applies in conjunction with AC application
Busbar support design	PLS 1600 PLUS
Number of poles	4-pole
Suitable for busbars	PLS 1600
With internal attachment	Yes
Center-to-center spacing of busbars	60 mm
Packaging unit	4 pc(s).
Net weight	2.2
Gross weight	2.321
Customs tariff number	85469010
EAN	4028177536760
ETIM 9	EC001166
ECLASS 8.0	27400607

# Approvals

---

Approvals

ABS  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK