Rittal – The System.

Faster - better - everywhere.





SV 9342.004 PLS Busbar Supports

State: 2025-10-31 (Source: rittal.com/ca-en)



SV 9342.004 - PLS Busbar Supports

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.



Features

Model No.	SV 9342.004
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Electrical UL ratings (SCCR)	65 kA - 480 V, support spacing 250 mm, busbars PLS 1600, circuit breaker max. 1200A, DIVQ/7
Note on Model No.:	The use of a base tray is required for UL applications. UL approval only applies in conjunction with AC application
Busbar support design	PLS 1600 PLUS
Number of poles	4-pole
Suitable for busbars	PLS 1600
With internal attachment	Yes
Center-to-center spacing of busbars	60 mm
Packaging unit	4 pc(s).
Net weight	2.2
Gross weight	2.321
Customs tariff number	85469010

© Rittal 2025

Features

EAN	4028177536760
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3