

Rittal – The System.

Faster – better – everywhere.



SV 9393.222

External display

State: 2026-01-30 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.222 - External display REM RD 96 for network analyzer REM 801

For configuration and display of parameters as well as measurement values of the REM 801 network analyzer and its expansion modules.

Features

Model No.	SV 9393.222
Supply includes	Display USB 2.0 connection cable (Type A to Type B plug), 1.8 meters long
Operating temperature range	-10 °C...55 °C
Storage temperature range	-25 °C...70 °C
Ambient humidity (non-condensing)	0...75 %
Relative humidity	0 %
Contamination level	2
Protection category IP to IEC 60529	Front IP 40
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.402
Customs tariff number	85389099
EAN	4028177984943

Approvals

Explanations	Declaration of conformity
--------------	---------------------------