

Rittal – The System.

Faster – better – everywhere.



SV 9393.230 Connection module

State: 2026-05-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.230 - Connection module REM 800-CON

For connecting remotely located measuring points.

Features

| | |
|--|--|
| Model No. | SV 9393.230 |
| Product description | For connecting remotely located measuring points. |
| Supply includes | 2 connection modules 2 bus connectors (left/right) 2 shield terminals 2 screw terminals 2 end brackets |
| Operating temperature range | -10 °C...55 °C |
| Storage temperature range | -25 °C...70 °C |
| Ambient humidity (non-condensing) | 5...25 % |
| Contamination level | 2 |
| Protection category IP to IEC 60529 | IP 20 |
| For support rail assembly | Yes |
| Connection of round conductors, fine wire with wire end ferrule | 0.2 - 1.5 mm ² |
| Connection of round conductors, fine wire without wire end ferrule | 0.2 - 1.5 mm ² |
| Connection of round conductors, single-wire | 0.2 - 1.5 mm ² |
| Connection of round conductors, multi-wire | 0.2 - 1.5 mm ² |
| Connection for round conductor | AWG 16 - 24 |
| Packaging unit | 2 pc(s). |
| Net weight | 0.36 kg |

Features

| | |
|-----------------------|----------------------------------|
| Gross weight | 0.366 kg |
| Customs tariff number | 85389099 |
| Product description | SV connection module REM 800-CON |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|