

**Rittal – The System.**

Faster – better – everywhere.



**PK 9505.000**

**PK Polycarbonate Housings**

State: 2025-08-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9505.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9505.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66

# Features

IK code	IK08
Dimensions	Width: 94 mm Height: 94 mm Depth: 81 mm
Operating temperature range	-35 °C...80 °C
Base material	Polycarbonate
Packaging unit	6 pc(s).
Net weight	1.32
Gross weight	1.441
Customs tariff number	94037000
EAN	4028177139138
ETIM 9	EC000261
ECLASS 8.0	27180101

# Approvals

Approvals	C-UL DNV-GL UL UL + C-UL (listed)
Explanations	Declaration of conformity