

Rittal – The System.

Faster – better – everywhere.



PK 9508.000

PK Polycarbonate Housings

State: 2026-04-02 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9508.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

| | |
|------------------------------------|--|
| Model No. | PK 9508.000 |
| Version | PK housing with closed cover |
| Product description | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment. |
| Material | Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene |
| Color | RAL 7035 |
| Supply includes | Housing with cover Cover screws Insulating bungs for wall mounting screws |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60529 | IP 66 |

Features

| | |
|-----------------------------|--|
| IK code | IK08 |
| Dimensions | Width: 130 mm Height: 94 mm Depth: 57 mm |
| Operating temperature range | -35 °C...80 °C |
| Base material | Polycarbonate |
| Packaging unit | 4 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 0.898 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | PK Polycarbonate enclosure, WHD: 130x94x57 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

Approvals

| | |
|--------------|--|
| Approvals | C-UL DNV-GL UL UL + C-UL (listed) |
| Explanations | Declaration of conformity |