Rittal – The System.

Faster – better – everywhere.





PK 9509.000 PK Polycarbonate Housings

State: 2025-11-09 (Source: rittal.com/ca-en)



PK 9509.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.







Features

Model No.	PK 9509.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66

© Rittal 2025

Features

IK08
Width: 130 mm Height: 94 mm Depth: 81 mm
-35 °C80 °C
Polycarbonate
4 pc(s).
1
1.17
94037000
4028177139299
EC000261
27180101

Approvals

Approvals	C-UL
	DNV-GL
	UL
	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3