


Rittal – The System.

Faster – better – everywhere.



PK 9512.000

PK Polycarbonate Housings

State: 2025-08-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9512.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9512.000
Version	PK housing with closed cover
Product description	Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.
Material	Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
Color	RAL 7035
Supply includes	Housing with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66

Features

IK code	IK08
Dimensions	Width: 180 mm Height: 94 mm Depth: 57 mm
Operating temperature range	-35 °C...80 °C
Base material	Polycarbonate
Packaging unit	2 pc(s).
Net weight	0.56
Gross weight	0.62
Customs tariff number	94037000
EAN	4028177139411
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	C-UL DNV-GL UL UL + C-UL (listed)
Explanations	Declaration of conformity