## Rittal – The System.

Faster – better – everywhere.





## PK 9516.000 PK Polycarbonate Housings

State: 2025-10-16 (Source: rittal.com/ca-en)



# PK 9516.000 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.







#### **Features**

PK 9516.000
PK housing with closed cover
Use in ambient temperature range: -35°C+80°C. The specified temperatures can be limited by the installed equipment.
Housing: Fiber-glass reinforced polycarbonate Cover gray: Fiberglass-reinforced polycarbonate, all-round foamed PU seal Cover screws: Polyamide Insulating bungs: Polythene
RAL 7035
Housing with cover Cover screws Insulating bungs for wall mounting screws
NEMA 4X
IP 66

© Rittal 2025

### Features

IK code	IK08
Dimensions	Width: 180 mm Height: 110 mm
	Depth: 165 mm
Operating temperature range	-35 °C80 °C
Base material	Polycarbonate
Packaging unit	2 pc(s).
Net weight	1.174
Gross weight	1.373
Customs tariff number	94037000
EAN	4028177139572
ETIM 9	EC000261
ECLASS 8.0	27180101

## **Approvals**

Approvals	C-UL
	DNV-GL
	UL
Explanations	Declaration of conformity

© Rittal 2025 3