

# Rittal – The System.

Faster – better – everywhere.



## SV 9615.100

# Mini-PLS Component Adaptor

State: 2026-04-28 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9615.100 - Mini-PLS Component Adaptor

Maximum rated current from 12 A to 100 A.

## Features

|                              |   |
|------------------------------|---|
| Model No.                    | SV 9615.100   |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Color                        | RAL 7035  |
| Connection cables (AWG)      | AWG 12  |
| Rated operating voltage      | 690 V, 3~   |
| Rated current max.           | 25 A  |
| Dimensions                   | Width: 45 mm<br>Height: 160 mm  |
| Support rails Qty/height     | 1 / 15 mm   |
| Packaging unit               | 1 pc(s).  |
| Net weight                   | 0.29 kg   |
| Gross weight                 | 0.329 kg  |
| Copper weight (kg per piece) | 0.041   |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| ECLASS 8.0                   | 27370304  |
| Product description          | SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x160 mm, support rail H: 15 mm |

## Approvals

|           |                        |
|-----------|------------------------|
| Approvals | UR + C-UR (recognized) |
|-----------|------------------------|

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK