Rittal - The System.

Faster – better – everywhere.





SV 9635.330 Component Adapters

State: 2025-11-22 (Source: rittal.com/ca-en)



SV 9635.330 - Component Adapters 3-pole

For assembly of switchgear and protective devices.

Features

Model No.	SV 9635.330
Version	Comfort
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 7035
Note	The technical data may vary for UL applications.
Rated current max.	16 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Electrical UL ratings	Rated operating voltage (max.) UL: 600 V AC
Connection cables (AWG)	AWG 14
Length of connection cable	160 mm
Support rails Qty/height	1 / 10 mm
Support rail type	Adjustable
Dimensions	Width: 45 mm Height: 160 mm Depth: 34.5 mm
Packaging unit	4 pc(s).
Net weight	0.44
Gross weight	0.494
Copper weight (kg per piece)	0.026

© Rittal 2025

Features

Customs tariff number	85369095
EAN	4028177817357
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3