

Rittal – The System.

Faster – better – everywhere.



SV 9635.360 Component Adapters

State: 2025-07-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.360 - Component Adapters 3-pole

For assembly of switchgear and protective devices.

Features

| | |
|------------------------------|--------------------------------------------------------------------------------------|
| Model No. | SV 9635.360 |
| Version | Comfort |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide Fire behavior corresponding to UL 94 |
| Color | RAL 7035 |
| Note | The technical data may vary for UL applications. |
| Rated current max. | 45 A |
| Rated operating voltage | 600 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Electrical UL ratings | Rated operating voltage (max.) UL: 600 V AC |
| Connection cables (AWG) | AWG 8 |
| Length of connection cable | 100 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | Adjustable |
| Dimensions | Width: 45 mm Height: 160 mm Depth: 34.5 mm |
| Packaging unit | 4 pc(s). |
| Net weight | 0.64 |
| Gross weight | 0.683 |
| Copper weight (kg per piece) | 0.062 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177817326 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |