

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.382 Component Adapters

State: 2025-08-30 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.382 - Component Adapters 1-pole

For assembly of switchgear and protective devices.

## Features

Model No.	SV 9635.382
Version	L2
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 7035
Note	Different adapter designs are required depending on the desired phase connection The technical data may vary for UL applications.
Rated current max.	63 A
Rated operating voltage	690 V (AC), 1~
Number of poles	1-pole
Connection cables (AWG)	AWG 8
Length of connection cable	100 mm
Support rails Qty/height	1 / 10 mm
Support rail type	Fixed
Dimensions	Width: 18 mm Height: 160 mm Depth: 35 mm
Packaging unit	6 pc(s).
Net weight	0.36
Gross weight	0.462
Copper weight (kg per piece)	0.021

# Features

Customs tariff number	85369095
EAN	4028177934559
ETIM 9	EC001531
ECLASS 8.0	27370304

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK