

Rittal – The System.

Faster – better – everywhere.



SV 9665.770

Cable entry flange

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9665.770 - Cable entry flange for roof plate

Cable entry gland for roof plates, with metric knockouts, seal membranes, cable entry glands, or solid.



Features

Model No.	SV 9665.770
Version	With sealing membranes 32 x Ø 7 – 16 mm, 4 x Ø 10 – 20 mm, 3 x Ø 14 – 26 mm
Product description	For simple, secure cable entry in the roof zone.
Material	Insulating material
Color	RAL 7035
Supply includes	Seal
Dimensions	Width: 250 mm Depth: 160 mm
Protection category IP to IEC 60529	IP 55
Packaging unit	1 pc(s).
Net weight	0.3 kg
Gross weight	0.341 kg
Customs tariff number	39269097
ETIM 9	EC000211
ECLASS 8.0	27142421

Features

Product description

SV Cable entry gland, with sealing membranes, 32x Ø 7-16 mm, 4x Ø 10-20 mm, 3x Ø 14-26 mm, insulating material