

Rittal – The System.

Faster – better – everywhere.



SV 9666.550 NH fuse switch module

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.550 - NH fuse switch module

For NH in-line fuse-switch disconnectors, sizes 00 to 3 (three-pin, 100/185 mm busbar center-to-center distance).

Features

Model No.	SV 9666.550
Product description	For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar center distance).
Material	Cover: Polystyrene Holder: Fiberglass-reinforced plastic
Color	RAL 7035
Supply includes	Assembly components
Note	In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules.
Dimensions	Width: 500 mm Height: 750 mm
Size	Width units (WU) @ 250 mm: 2 Height units (U) @ 150 mm: 5
For size	8 x Gr. 00 4 x Gr. 1 4 x Gr. 2 4 x Gr. 3
Suitable for Model No.	9677.XXX
Suitable for busbars	40 x 10 50 x 10 60 x 10
Center-to-center spacing of busbars	185 mm
Packaging unit	1 pc(s).
Net weight	3.84 kg

Features

Gross weight	3.89 kg
Customs tariff number	85369095
ETIM 9	EC001893
ECLASS 8.0	27400608
Product description	SV NH fuse-switch disconnecter module (ISV), 2 WU (500 mm), 5 U (750 mm), for 8 x size 00, 4 x size 1-3, (SV 9346XXX, 185 mm)

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---