Rittal - The System.

Faster – better – everywhere.





SV 9666.570 NH fuse switch module

State: 2025-11-13 (Source: rittal.com/ca-en)



SV 9666.570 - NH fuse switch module

For NH in-line fuse-switch disconnectors, sizes 00 to 3 (three-pin, 100/185 mm busbar center-to-center distance).

Features

Model No.	SV 9666.570
Product description	For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar center distance).
Material	Cover: Polystyrene Holder: Fiberglass-reinforced plastic
Color	RAL 7035
Supply includes	Assembly components
Note	In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules.
Dimensions	Width: 250 mm Height: 450 mm
Size	Width units (WU) @ 250 mm: 1 Height units (U) @ 150 mm: 3
For size	3 x Gr. 00
Suitable for Model No.	9346.020 9346.030
Suitable for busbars	40 x 10
Center-to-center spacing of busbars	100 mm
Packaging unit	1 pc(s).
Net weight	1.7
Gross weight	1.83
Customs tariff number	85369095

© Rittal 2025

Features

EAN	4028177676459
ETIM 9	EC001893
ECLASS 8.0	27400608

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3