

# Rittal – The System.

Faster – better – everywhere.



## SV 9666.583 NH fuse switch module

State: 2026-04-03 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9666.583 - NH fuse switch module

For NH in-line fuse-switch disconnectors, sizes 00 to 3 (three-pin, 100/185 mm busbar center-to-center distance).

## Features

Model No.	SV 9666.583
Product description	For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar center distance).
Material	Cover: Polystyrene Holder: Fiberglass-reinforced plastic
Color	RAL 7035
Supply includes	Assembly components
Note	In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules.
Dimensions	Width: 750 mm Height: 450 mm
Size	Width units (WU) @ 250 mm: 3 Height units (U) @ 150 mm: 3
For size	10 x Gr. 00
Suitable for Model No.	9346.020 9346.030
Suitable for busbars	40 x 10
Center-to-center spacing of busbars	100 mm
Packaging unit	1 pc(s).
Net weight	3.33 kg
Gross weight	3.34 kg
Customs tariff number	85369095

# Features

---

ETIM 9	EC001893
ECLASS 8.0	27400608
Product description	SV NH fuse-switch disconnecter module (ISV), 3 WU (750 mm), 3 U (450 mm), for 10 x size 00, (SV 9346XXX, 100 mm)

---

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---