

# Rittal – The System.

Faster – better – everywhere.



## TS 9672.143

## Partial Doors

State: 2026-04-01 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 9672.143 - Partial Doors for TS

Door may be optionally hinged on the right or left.



## Features

|                     |   |
|---------------------|---|
| Model No.           | TS 9672.143   |
| Product description | Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high. |
| Material            | Carbon steel, 2 mm  |
| Surface finish      | Textured paint  |
| Color               | RAL 7035  |
| Supply includes     | Cross member<br>Hinges<br>Lock components<br>Assembly components  |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 400 mm<br>Height: 300 mm         |
| Suitable for                        | Width: = 400 mm                         |
| Protection category IP to IEC 60529 | IP 54 for a completed enclosure         |
| Packaging unit                      | 1 pc(s).                                |
| Net weight                          | 2.8 kg                                  |
| Gross weight                        | 3 kg                                    |
| Customs tariff number               | 94039910                                |
| ETIM 9                              | EC002525                                |
| ECLASS 8.0                          | 27182204                                |
| Product description                 | SV Partial door, WH: 400x300 mm, for TS |