

Rittal – The System.

Faster – better – everywhere.



TS 9672.161 Partial Doors

State: 2026-04-02 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

TS 9672.161 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

Model No.	TS 9672.161
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm
Surface finish	Textured paint
Color	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly components

Features

Dimensions	Width: 600 mm Height: 150 mm
Suitable for	Width: = 600 mm
Protection category IP to IEC 60529	IP 54 for a completed enclosure
Packaging unit	1 pc(s).
Net weight	2.572 kg
Gross weight	2.772 kg
Customs tariff number	94032080
ETIM 9	EC002525
ECLASS 8.0	27182204
Product description	SV Partial door, WH: 600x150 mm, for TS