Rittal – The System.

Faster – better – everywhere.





POWER DISTRIBUTION > CLIMATE CONTROL

State: 2025-11-11 (Source: rittal.com/ca-en)

TS 9672.188 - Partial Doors for TS

Door may be optionally hinged on the right or left.





Features

Model No.	TS 9672.188
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm
Surface finish	Textured paint
Color	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly components

© Rittal 2025 2

Features

Dimensions	Width: 800 mm Height: 800 mm
Suitable for	Width: = 800 mm
Protection category IP to IEC 60 529	IP 54 for a completed enclosure
Packaging unit	1 pc(s).
Net weight	12.8
Gross weight	12.9
Customs tariff number	94039910
EAN	4028177697836
ETIM 9	EC002525
ECLASS 8.0	27182204

© Rittal 2025 3