Rittal - The System.

Faster - better - everywhere.





SV 9677.705 Component Adapters

State: 2025-12-13 (Source: rittal.com/ca-en)



SV 9677.705 - Component Adapters Screw fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.705
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
For bar systems with center-to- center spacing	185 mm
Cable outlet	Bottom
Installation type	Screw attachment
Number of poles	3-pole
Rated current max.	1,000 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal for fastening to perforated busbars. Note that no cover sections are fitted in the vicinity of the device.
Dimensions	Width: 300 mm Height: 652 mm
Suitable for busbars	Height: 10 mm
To fit manufacturer (model)	ABB (Tmax T7 - 800 A/1000 A) Eaton (NZM4 - 800 A/1000 A) Schneider Electric (NS - 800 A/1000 A) Siemens (3VA27 - 800 A/1000 A)
Packaging unit	1 pc(s).
Net weight	13.8
Gross weight	14.35

© Rittal 2025

Features

Copper weight (kg per piece)	7.814
Customs tariff number	85369095
EAN	4028177707085
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3