

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.905

## Connection Adapters

State: 2026-02-08 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.905 - Connection Adapters

For connecting round conductors. For busbar systems with 185 mm center-to-center distance.

## Features

Model No.	SV 9677.905
Material	Chassis: Fiberglass-reinforced polyester Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Contact hazard protection cover
For bar systems with center-to-center spacing	185 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M12
Number of poles	3-pole
Rated current max.	1,400 A
Rated operating voltage	690 V, 3~
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Dimensions	Width: 100 mm Height: 960 mm
Connection of round conductors	6 - 300 mm <sup>2</sup>
Suitable for busbars	Height: 10 mm
Packaging unit	1 pc(s).
Net weight	11
Gross weight	11.5
Copper weight (kg per piece)	4.41
Customs tariff number	85369010
EAN	4028177705296

# Features

---

ETIM 9 EC001531

---

ECLASS 8.0 27370304

# Approvals

---

Explanations Declaration of conformity  
Declaration of conformity UK