


Rittal – The System.

Faster – better – everywhere.



SV 9681.594

Roof plates for cable entry glands

State: 2026-01-31 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

SV 9681.594 - Roof plates for cable entry glands for VX, VX IT

For enclosures without roof plate and to replace the standard roof on other enclosures.

Features

| | |
|---------------------------------------|--|
| Model No. | SV 9681.594 |
| Product description | For enclosures without roof plate and to replace the standard roof. |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Textured paint |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Number of required cable entry glands | 3 |
| Suitable for | Width: = 850 mm Depth: = 400 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 1.8 |
| Gross weight | 4.04 |
| PCF/VE (cradle-to-gate) | 15.4 kg CO ₂ eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177926639 |
| ETIM 9 | EC000744 |
| ECLASS 8.0 | 27182405 |

Approvals

Explanations

Declaration of conformity UK