


Rittal – The System.

Faster – better – everywhere.



SV 9682.188 Partial door

State: 2025-09-15 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9682.188 - Partial door for VX

Door may be optionally hinged on the right or left.

Features

| | |
|-------------------------------------|---|
| Model No. | SV 9682.188 |
| Product description | Suitable for VX enclosures instead of a door or rear panel. The partial doors can be combined with each other. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. Installation of the SZ 2305.000 monitor frame is possible in doors without a viewing window (height 600–1,000 mm). The standard double-bit lock insert may be exchanged for Type A lock inserts. |
| Material | Carbon steel, 2 mm |
| Surface finish | Textured paint |
| Color | RAL 7035 |
| Supply includes | Partial door Cross member Hinges Lock components Assembly components |
| Note | Swing angle of partial doors max. 130° |
| Lock | No. of locks: 2 |
| Dimensions | Width: 800 mm Height: 800 mm |
| Suitable for | Width: = 800 mm |
| Protection category IP to IEC 60529 | IP 54 |
| Packaging unit | 1 pc(s). |
| Net weight | 12.86 |
| Gross weight | 13.16 |
| PCF/VE (cradle-to-gate) | 50.1 kg CO2 eq (Cat B) |

Features

| | |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177928916 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) UL + C-UL - FTТА |
| Explanations | Declaration of conformity Declaration of conformity UK |