

# Rittal – The System.

Faster – better – everywhere.



## SV 9683.643

# Partial Mounting Panel

State: 2026-06-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9683.643 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

## Features

Model No.	SV 9683.643
Version	Solid
Product description	For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible.
Material	Carbon steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly components
For compartment height	300 mm
Dimensions	Width: 302 mm Height: 293 mm
Suitable for	Width: = 400 mm
Packaging unit	1 pc(s).
Net weight	2.42 kg
Gross weight	2.82 kg
PCF/VE (cradle-to-gate)	10.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC000213
ECLASS 8.0	27400613

# Features

---

Product description

SV Partial mounting plate, WH: 302x293 mm, solid, for VX (W: 400 mm)